

Product data sheet

Characteristics

56P450-RO

56 Series plug top straight 4 pin 50A 500 V IP66



Main

Range of product	Series 56
Product brand	Clipsal

Complementary

[In] rated current	50 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Colour	Resistant orange
Material	Plastic
Connections - terminals	Screw terminal
Cable entry	Cable gland
Plug, socket, control station shape	Straight
Pin arrangement	P
Duration	7 h

Packing Units

Package 1 Weight	404.000 g
Package 1 Height	90.000 mm
Package 1 width	95.000 mm
Package 1 Length	199.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.