

Product data sheet

Characteristics

56PA320-EO

56 Series Plug - 3 Pin - 20A - 250V - Angled



Main

| | |
|---------------------------|---------------------|
| Range | Clipsal - 56 Series |
| Range of product | Series 56 |
| Product brand | Clipsal |
| Product or component type | Plug |
| Device application | Power supply |

Complementary

| | |
|-------------------------------------|---|
| [In] rated current | 20 A |
| Poles description | 1P + N + E |
| [Ue] rated operational voltage | 250 V AC 50 Hz conforming to EN 60309-2 |
| Colour | Orange (RAL 2004) |
| Material | Plastic |
| Plug, socket category | Low voltage |
| Material | Polycarbonate: housing |
| Outlet standard | Industrial |
| Connections - terminals | Screw terminal 1...6 mm ² |
| Wire stripping length | 45 Mm 12 mm |
| Contacts material | Pins: brass |
| Cable entry | Cable gland |
| Thread type | M25 |
| Plug, socket, control station shape | Angled |
| Pin arrangement | H |
| Duration | 6 h |
| Net weight | 0.32 kg |
| Height | 78 mm |
| Width | 126.5 mm |
| Depth | 158 mm |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|-----------------------------|
| Standards | AS/NZS 3123 |
| IP degree of protection | IP66 conforming to AS 60529 |
| Ambient air temperature for operation | -25...75 °C |

Packing Units

| | |
|------------------|------------|
| Package 1 Weight | 316.000 g |
| Package 1 Height | 80.000 mm |
| Package 1 width | 95.000 mm |
| Package 1 Length | 190.000 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |