

Product data sheet

Characteristics

56RC-GY

Residual Current Circuit Breaker, Clipsal - 56 Series, 2 Pole, 20A

Main

Range	Clipsal - 56 Series
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Device application	Protection
Poles description	2P
[In] rated current	20 A
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A

Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
Control type	Push-button
Protection type	Earth-leakage protection
Installation direction	Vertical
Mounting mode	Surface mounted
Mounting support	DIN rail
Size	107 x 101 x 101 mm conforming to DIN 43880
Height	101 mm
Width	101 mm
Depth	101 mm
Net weight	0.58 kg
Colour	Grey (RAL 7035)
Material	Polycarbonate
Number of gangs	1 gang
Cable cross section	1...10 mm ²

Environment

IP degree of protection	IP66
Ambient air temperature for operation	-25...75 °C
Electrical insulation class	Class II

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.8 cm
Package 1 Width	10.6 cm
Package 1 Length	11.6 cm
Package 1 Weight	588.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes