

## Product data sheet

### Characteristics

# 56RCLE-GY

## Residual Current Circuit Breaker, Clipsal - 56 Series, 2 Pole, 20A, 30mA, Less Enclosure



### Main

Range	Clipsal - 56 Series
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Device application	Protection
Poles description	2P
[In] rated current	20 A
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A

### Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
Control type	Push-button
Protection type	Earth-leakage protection
Installation direction	Vertical
Mounting mode	Surface mounted
Mounting support	DIN rail
Size	107 x 101 x 101 mm conforming to DIN 43880
Height	101 mm
Width	101 mm
Depth	65 mm
Net weight	0.3 kg
Colour	Grey (RAL 7035)
Material	Polycarbonate
Number of gangs	1 gang
Cable cross section	1...10 mm <sup>2</sup>

### Environment

IP degree of protection	IP66
Ambient air temperature for operation	-25...75 °C
Electrical insulation class	Class II

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	10.3 cm
Package 1 Length	10.2 cm
Package 1 Weight	298.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations