

Product data sheet

Characteristics

56SW163LE-RW

SURFACE SWITCH PVC IP66 1 GANG 63A LESS ENCLOSURE



Main

Range of product	Series 56
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	1-pole
[Icm] rated short-circuit making capacity	2.1 kA
Control type	Rotary knob
Number of poles	1
Device mounting	Surface
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	63 A
Marking	ON-OFF
Marking location	Marking on surface
[Icw] rated short-time withstand current	1.5 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV

Environment

Standards	AS/NZS 3123 AS/NZS 3947-3
-----------	------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.25 cm
Package 1 Width	9.95 cm
Package 1 Length	9.95 cm
Package 1 Weight	0.267 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins