

## Product data sheet

### Characteristics

## 56SW210/2LE-GY

Clipsal - 56 Series, Surface Switch, IP66 1  
Gang Double Pole 2 Way Less Enclosure



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Switch function	2-pole
Poles description	2P
[Icm] rated short-circuit making capacity	1 kA
Control type	Rotary knob
Number of poles	2
Device mounting	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	10 A
Marking	I-II
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	72 mm
Net weight	1 kg
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
[Icw] rated short-time withstand current	1.2 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV
Motor M-rating AS3133	M40 at 250 V

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	10.5 cm
Package 1 Length	10 cm
Package 1 Weight	196 g

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>