

Product data sheet

Characteristics

56RCLE-GY

Residual current circuit breaker, Clipsal - 56 Series, 2P, 20 A, 30 mA, 250 V



Main

Range	Clipsal - 56 Series
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Device application	Protection
Poles description	2P
[In] rated current	20 A
Earth-leakage sensitivity	30 mA

Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
Control type	Push-button
Protection type	Earth-leakage protection
Installation direction	Vertical
Mounting mode	Surface mounted
Mounting support	DIN rail
Size	107 x 101 x 101 mm conforming to DIN 43880
Height	101 mm
Width	101 mm
Depth	65 mm
Net weight	0.3 kg
Colour	Grey (RAL 7035)
Material	Polycarbonate
Number of gangs	1 gang
Cable cross section	1...10 mm ²

Environment

IP degree of protection	IP66
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	10.3 cm
Package 1 Length	10.2 cm
Package 1 Weight	298.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile