

Product data sheet

Characteristics

56SC410RC-GY

56 Series Switched Socket Outlet with RCD -
10A - 4 Pin - 500V - 30mA RCD - Grey



Main

Range	Clipsal - 56 Series
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Control type	Push-button
[In] rated current	10 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	4 gangs
Installation direction	Vertical
Material	Polycarbonate
Connections - terminals	Screw terminal cable(s) 1.5...16 mm ²
Mounting mode	Surface mounted
Depth	135 mm
Width	204 mm
Height	204 mm
Net weight	2.092 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2019.5 g
Package 1 Height	115 mm
Package 1 width	205 mm
Package 1 Length	210 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile