

## Product data sheet

### Characteristics

# 56SW250LE-GY

## 56 Series - Switch - 2 Pole - 50A - 250V - Less Enclosure - grey



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Switch function	2-pole
Poles description	2P
[Icm] rated short-circuit making capacity	2.1 kA
Control type	Rotary knob
Number of poles	2
Device mounting	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	50 A
Marking	ON-OFF
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	72 mm
Product weight	0.001 kg
Breaking capacity	50 kA
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
[Icw] rated short-time withstand current	1.5 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV
Motor M-rating AS3133	M250 at 250 V

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg
Package 1 Height	10.7 cm
Package 1 width	10.1 cm
Package 1 Length	7.2 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>