

## Product data sheet

### Characteristics

# 56SO310A-GY

## 56 Series Socket - 3 Pin - 10A - 250V - Auto Switched - Grey



### Main

|                           |                        |
|---------------------------|------------------------|
| Range of product          | Series 56              |
| Range                     | Clipsal - 56 Series    |
| Product brand             | Clipsal                |
| Product or component type | Socket-outlet          |
| Device application        | Power supply           |
| Colour                    | Grey (RAL 7035)        |
| Outlet standard           | Australian/New Zealand |

### Complementary

|                                     |   |
|-------------------------------------|---|
| Plug, socket category               | Low voltage   |
| Plug, socket, control station shape | Straight  |
| Device mounting                     | Surface   |
| Mounting mode                       | External mounting   |
| [In] rated current                  | 10 A  |
| [Ue] rated operational voltage      | 250 V AC 50 Hz conforming to EN 60309-2                         |
| Poles description                   | 1P + N + E  |
| Voltage colour                      | Blue  |
| Duration                            | 6 h   |
| Material                            | Polycarbonate: cover  |
| Contacts material                   | Screws: brass   |
| Connections - terminals             | Screw terminals 1.5...6 mm <sup>2</sup> rigid or stranded cable |
| Tightening torque                   | 0.8 N.m   |
| Socket number                       | 1   |
| Socket-outlet type                  | A   |
| Outlet standard                     | Industrial  |
| Cable outer diameter                | 7...16 mm   |
| Net weight                          | 0.4 kg  |
| Depth                               | 77 mm   |
| Width                               | 101 mm  |
| Height                              | 107 mm  |
| Targeted country                    | Australia   |

### Environment

|                                       |                              |
|---------------------------------------|------------------------------|
| IP degree of protection               | IP66 conforming to AS 60529  |
| Ambient air temperature for operation | -25...75 °C                  |
| Standards                             | AS/NZS 3112<br>AS/NZS 4417.1 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Weight             | 409.0 g |
| Package 1 Height             | 9.2 cm  |
| Package 1 width              | 10.7 cm |
| Package 1 Length             | 11 cm   |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |