

Product data sheet

Characteristics

56SO315LE-GY

Socket Outlet, Clipsal - 56 Series, Surface 3
PIN 15A Less Enclosure



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard deviation	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals 2.5...6 mm ² rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	B
Outlet standard	Industrial
Cable entry	Tapped entry
Net weight	0.22 kg
Depth	64 mm
Width	101 mm
Height	107 mm
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 4417.1 AS/NZS 3112

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	10.0 cm
Package 1 Length	10.4 cm
Package 1 Weight	216.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	45
Package 2 Weight	9.9 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	1080
Package 3 Weight	237.6 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes