

Product data sheet

Characteristics

56SO316/6LE-GY

56 Series Socket - 3 Pin - 16A - 250V - Less Enclosure - Grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	16 A
[Ue] rated operational voltage	250 V AC 50 Hz
Poles description	1P + N + E
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Outlet standard	Industrial
Net weight	0.24 kg
Width	101 mm
Height	107 mm
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
Standards	IEC 309

Packing Units

Package 1 Weight	242.000 g
Package 1 Height	108.000 mm
Package 1 width	100.000 mm
Package 1 Length	105.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile