

Product data sheet

Characteristics

56SO4ELP15-GY

56 Series Portable 4 Socket Outlets with RCD -15A -3 Pin -250V -30mA RCD -Grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Control type	Push-button
Mounting mode	External mounting
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Network number of phases	1 phase
Number of gangs	6 gangs
Voltage colour	Blue
Duration	6 h
Material	Polycarbonate
Socket number	1
Net weight	3.252 kg
Depth	105 mm
Width	294 mm
Height	243 mm
Targeted country	Australia

Environment

IP degree of protection	IP56
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.117 kg
Package 1 Height	11.5 cm
Package 1 width	40.5 cm
Package 1 Length	6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile