

## Product data sheet

### Characteristics

# 56SW350LE-GY

## Surface Switch, Clipsal - 56 Series, IP66 1 Gang 3 Pole 50A Less Enclosure



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate
Device application	Control
Handle colour	Grey
Suitability for isolation	Yes
Colour	Cover: grey

### Complementary

Poles description	3P
[Icm] rated short-circuit making capacity	2.1 kA
Control type	Rotary knob
Number of poles	3
Installation Type	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	50 A
Marking	ON-OFF
Marking location	Marking on surface
Breaking capacity	50 kA
Targeted country	Australia
Height	107 mm
Width	101 mm
Depth	69 mm
Net weight	0.46 kg
Motor M-rating AS3133	M250 at 500 V
[Uimp] rated impulse withstand voltage	4 kV
[Icw] rated short-time withstand current	1.5 kA for 1 s
Switch function	3-pole
Rotary handle padlocking	2 padlocks 8 mm

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	10.0 cm
Package 1 Length	9.9 cm
Package 1 Weight	364.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations