

Product data sheet

Characteristics

56SW420COLE-GY

Clipsal - 56 Series, Surface Switch, 4P 20A
C/Over Less Enclosure (With 7 Series
Mechanism)



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

Complementary

Switch function	4-pole
Poles description	4P
[Icm] rated short-circuit making capacity	1.7 kA
Control type	Rotary knob
Number of poles	4
Device mounting	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	20 A
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	119 mm
Net weight	0.001 kg
Breaking capacity	20 kA
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
[Icw] rated short-time withstand current	0.8 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV


Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes