

Product data sheet

Characteristics

56SSR/3-GY

Sunset Switch, 3 Wire, 240VAC, 10A, 56 Series



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Sunset switch
Device presentation	Basic element
Device application	Control
Colour	Enclosure: grey (RAL 7035) Cover: opal

Complementary

Control type	Electronic
Device mounting	Surface
Fixing mode	By screws
Cable entry	1 rear entry of 20...25 mm diameter
Material	PVC (polyvinyl chloride) Polycarbonate
Surface finish	Gloss
Installation direction	Horizontal Vertical
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	10 AX
Time delay range	2...12 h
Light intensity adjustment	20...500 lux
Marking	Without marking
Height	101 mm
Width	101 mm
Depth	70 mm
Quantity per set	Set of 1
Type of packing	Carton

Environment

Ambient air temperature for operation	45 °C
IP degree of protection	IP66
Standards	AS/NZS 3133 AS/NZS 3100 IEC 60669-2-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.7 cm
Package 1 Width	10.5 cm
Package 1 Length	11.0 cm
Package 1 Weight	398.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	4.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information