

Product data sheet

Characteristics

56SWAUX15

Clipsal - 56 Series, Industrial Switchgear Accessories, Auxilliary Switch, 15A



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Auxiliary switch
Device presentation	Basic element
Device application	Control

Complementary

Poles description	1P
Device mounting	Surface
Local signalling	without
[Ue] rated operational voltage	250 V
Rated current	15 A
Net weight	0.016 kg
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm

Environment

Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	2.7 cm
Package 1 Length	5.5 cm
Package 1 Weight	13 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	70 cm
Package 2 Width	102 cm
Package 2 Length	103 cm
Package 2 Weight	130 g
Unit Type of Package 3	CAR
Number of Units in Package 3	300
Package 3 Height	214 cm
Package 3 Width	297 cm
Package 3 Length	429 cm
Package 3 Weight	300 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations