

Product data sheet

Characteristics

56SSW15LE-GY

Surface Switch, Clipsal - 56 Series, IP66 1 Gang Single Pole 15A Less Enclosure

Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate
Device application	Control
Handle colour	Grey
Suitability for isolation	No
Colour	Cover: grey

Complementary

Poles description	1P
Control type	Sliding type
Number of poles	1
Installation Type	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	15 A
Marking	ON-OFF
Marking location	Marking on surface
Targeted country	Australia
Height	107 mm
Width	101 mm
Depth	48 mm
Net weight	0.18 kg
Motor M-rating AS3133	M80 at 250 V
Switch function	1-pole
Rotary handle padlocking	2 padlocks 8 mm

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP56 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.7 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	141.0 g

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	2