

## Product data sheet

### Characteristics

# 56SW110-CG

## Surface Switch, 1 Gang, 250VAC, 10A



### Main

|                           |                                     |
|---------------------------|-------------------------------------|
| Range of product          | Series 56                           |
| Range                     | Clipsal - 56 Series                 |
| Product brand             | Clipsal                             |
| Product or component type | Switch                              |
| Device presentation       | Basic element with full cover plate |
| Device application        | Control                             |
| Colour                    | Cover: chemical grey                |
| Handle colour             | Grey                                |
| Suitability for isolation | No                                  |

### Complementary

|                                |                    |
|--------------------------------|--------------------|
| Switch function                | 1-pole             |
| Poles description              | 1P                 |
| Control type                   | Rotary knob        |
| Number of poles                | 1                  |
| Device mounting                | Surface            |
| Fixing mode                    | By screws          |
| Material                       | PC (polycarbonate) |
| Tightening torque              | 0.8 N.m            |
| Local signalling               | without            |
| [Ue] rated operational voltage | 250 V AC 50 Hz     |
| Rated current                  | 10 A               |
| Marking                        | ON-OFF             |
| Marking location               | Marking on surface |
| Height                         | 107 mm             |
| Width                          | 101 mm             |
| Depth                          | 83 mm              |
| Net weight                     | 0.46 kg            |
| Breaking capacity              | 10 kA              |
| Targeted country               | Australia          |
| Rotary handle padlocking       | 2 padlocks 8 mm    |
| Motor M-rating AS3133          | M80 at 250 V       |

### Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Ambient air temperature for operation | -25...75 °C                 |
| IP degree of protection               | IP66 conforming to AS 60529 |
| Standards                             | AS/NZS 3133                 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | Db      |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 9.2 cm  |
| Package 1 Width              | 10.6 cm |
| Package 1 Length             | 10.8 cm |
| Package 1 Weight             | 384.0 g |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |