

## Product data sheet

### Characteristics

# 56SWT216LE-GY

Switch Surface Timer, Clipsal - 56 Series,  
Double Pole Less Enc



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate
Device application	Control
Handle colour	Grey
Suitability for isolation	No
Colour	Cover: grey

### Complementary

Poles description	2P
Control type	Rotary knob
Number of poles	2
Installation Type	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	16 A
Marking	Without marking
Targeted country	Australia
Height	107 mm
Width	101 mm
Product weight	0.32 kg
Switch function	2-pole
Rotary handle padlocking	2 padlocks 8 mm

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	80 cm
Package 1 Width	95 cm
Package 1 Length	95 cm
Package 1 Weight	0.32 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	24

Package 2 Height	270 cm
Package 2 Width	350 cm
Package 2 Length	450 cm
Package 2 Weight	24 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>