

Product data sheet

Characteristics

6220-0

Airflow, Performance Exhaust Fan, Ceiling Mount, 254mm, Axial



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	240 V AC
Air flow	800 m3/h
Diameter	254 mm impeller:
Power consumption in W	38 W
[In] rated current	0.17 A full load

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	33.0 cm
Package 1 Length	33.0 cm
Package 1 Weight	2385.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile