

Product data sheet

Characteristics

6220-0

Airflow, Performance Exhaust Fan, Ceiling Mount, 254mm, Axial



Main

Range of product	Airflow
Product brand	Clipsal

Complementary

[Ue] rated operational voltage	240 V AC
Air flow	800 m3/h
Diameter	254 mm impeller:
Power consumption in W	38 W
[In] rated current	0.17 A full load

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	33.0 cm
Package 1 Length	33.0 cm
Package 1 Weight	2385.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile