

Product data sheet

Characteristics

7GF10/D52/U

7 Series Cam Switches, 2 Pole, Changeover
Switch Marked Man / Off / Auto



Main

| | |
|-------------------------|----------------------|
| Product brand | Clipsal |
| Range of product | Series 7 |
| Electrical circuit type | Changeover contactor |

Complementary

| | |
|---------------------------------------------|----------------------|
| Switch function | 3-way |
| Mounting holes diameter | 9 mm |
| [Us] rated supply voltage | 415 V DC |
| Number of contacts | 3 |
| Connector type | Screw terminals |
| [Ui] rated insulation voltage | 480 V AC |
| [Ith] conventional free air thermal current | 10 A |
| Number of poles | 2 |
| Rated operational power in W | 3 kW |
| Switching angle | 60 ° |
| Fuse type | 3 KA, gG 3 kA, gL |
| Maximum short-circuit current | 10 A |

Environment

| | |
|-------------------------|------|
| IP degree of protection | IP20 |
|-------------------------|------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.5 cm |
| Package 1 Width | 5.5 cm |
| Package 1 Length | 11.3 cm |
| Package 1 Weight | 73 g |

Offer Sustainability

| | |
|-------------------|---------------------|
| EU RoHS Directive | Under investigation |
|-------------------|---------------------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.