

Product data sheet

Characteristics

7GF20/68/U

SWITCH CAM VOLTMETER SELECT



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[Ui] rated insulation voltage	480 V AC
[Ith] conventional free air thermal current	20 A
Rated operational power in W	7.5 kW
Fuse type	5 KA, gG 5 kA, gL
Maximum short-circuit current	20 A

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Package 1 Weight	1.000 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------