

Product data sheet

Characteristics

7GN25/D11/U

7 Series Cam Switches, Switch Cam Reversing

Single, 3 Pole, 25A



Main

Product brand	Clipsal
Range of product	Series 7
Electrical circuit type	Changeover contactor

Complementary

Switch function	3-way
Mounting holes diameter	12 mm
[Us] rated supply voltage	415 V DC
Number of contacts	3
Connector type	Screw terminals
[Ith] conventional free air thermal current	25 A
Number of poles	3
Switching angle	60 °

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	5.5 cm
Package 1 Length	11.4 cm
Package 1 Weight	149 g

Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations