

Product data sheet

Characteristics

8010E13M-WE

SOCKET OUTLET BRITISH 250V, 13A MOD WE



Main

Range of product	Series 80
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
[In] rated current	13 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	27.5 mm
Width	49.8 mm
Height	44.8 mm

Environment

Standards	BS 1363-2 AS/NZS 60884.1
-----------	-----------------------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	4.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	0.05 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.