

Product data sheet

Characteristics

A9C15409

Acti9 centralized control and remote indication - iATLc+s



Main

Range of product	Acti 9
Device short name	iATLc+s
Product or component type	Centralized control and remote indication auxiliary
Signal contacts composition	1 C/O
Signalling circuit voltage	24 V AC/DC: 10 mA 12...240 V AC: 50/60 Hz 6 A 12...24 V DC: 6 A 15...240 V AC: 50/60 Hz 2 A 13...24 V DC: 2 A
[Uc] control circuit voltage	24...240 V AC 50/60 Hz

Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Mounting mode	Fixed, on right side of TL
Mounting support	DIN rail
9 mm pitches	2
Height	86 mm
Width	18 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals 0.5...4 mm ² - rigid Tunnel type terminals 0.5...4 mm ² - rigid - with cable end Tunnel type terminals 1...4 mm ² - flexible Tunnel type terminals 1...4 mm ² - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti9 iTL iTL Acti9 iTL iTLi Acti9 iTL iTLs
Product compatibility	ITL (32 A) ITL (16 A)

Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C
Standards	EN/IEC 60669-2-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	74.0 g
Package 1 Height	2.9 cm
Package 1 width	8 cm
Package 1 Length	9 cm
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Weight	6.391 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	656.0 g
Package 3 Height	8.5 cm
Package 3 width	9.2 cm
Package 3 Length	26.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------