

Product data sheet

Characteristics

A9C15914

Remote indication auxiliary, Acti9 iACTs, 1 NO
+ 1 NC



Main

Range of product	ICT
Range	Acti 9
Device short name	IACTs
Product or component type	Remote indication auxiliary
Signal contacts composition	1 NO + 1 NC

Complementary

Signalling circuit voltage	24 V AC/DC: 10 mA 230 V AC: 50/60 Hz 5 A 230 V AC: 50/60 Hz 2 A 130 V DC: 1 A
[Uc] control circuit voltage	24...240 V AC 50/60 Hz 24...130 V DC
Range compatibility	Acti 9 iCT
[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Mounting mode	Fixed, on the right of CT
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	1
Height	81 mm
Width	9 mm
Depth	68 mm
Colour	White
Auxiliary connection terminal	Tunnel type terminals 2 cable(s) flexible 2.5 mm ² Tunnel type terminals 2 cable(s) rigid 1.5 mm ² Tunnel type terminals 1 cable(s) rigid 1.5...2.5 mm ² Tunnel type terminals 1 cable(s) flexible 1.5...2.5 mm ²
Wire stripping length	9 mm
Tightening torque	0.8 N.m
Product compatibility	ICT
Market segment	Small commercial Residential
Compatibility code	IACTs

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN 60947-5
IP degree of protection	IP20 IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------