

## Product data sheet

### Characteristics

# A9C18308

## Acti9, double control input auxiliary iACTc 230...240 V AC



### Main

Range	Acti9
Product or component type	Double control input auxiliary
Device short name	iACTc
[Uc] control circuit voltage	230...240 V AC 50/60 Hz impulse 250 ms 230...240 V AC 50/60 Hz maintained
[Us] rated supply voltage	220...240 V AC at 50/60 Hz

### Complementary

Maximum output current	0.2 A holding 2 A inrush
Hold-in power consumption in VA	3 VA
Mounting mode	Fixed, on the left of CT
Mounting support	DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	60 mm
Colour	White
Overvoltage category	III
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	440 V
Standards	IEC/EN 61095
Connections - terminals	Control circuit: tunnel type terminals 2 cable(s) 2.5 mm <sup>2</sup> flexible Control circuit: tunnel type terminals 2 cable(s) 1.5 mm <sup>2</sup> rigid Control circuit: tunnel type terminals 1 cable(s) 1.5...2.5 mm <sup>2</sup> rigid Control circuit: tunnel type terminals 1 cable(s) 1.5...2.5 mm <sup>2</sup> flexible with ferrule Control circuit: yellow clips
Wire stripping length	9 mm
Tightening torque	0.8 N.m
Range compatibility	Acti9 Acti9 iCT
Market segment	Small commercial Residential
Compatibility code	iACTc

### Environment

IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	7.9 cm
Package 1 Length	9.0 cm
Package 1 Weight	86.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.277 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------