

Product data sheet

Characteristics

56TCDB-GY

Clipsal - 56 Series, Timer Switch, 240VAC, 16A



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Time switch
Assembly Type	Basic element with full cover plate
Device application	Control
Outlet standard	Australian/New Zealand
Colour	Grey (RAL 7035)
Plug, socket category	Low voltage

Complementary

Poles description	1P + N + E
Installation Type	Surface
Material	Polycarbonate: cover
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	16 A
Protection type	Without protection
Marking	Without marking
Targeted country	Australia
Height	101 mm
Width	101 mm
Depth	102 mm
Net weight	0.604 kg
Contacts material	Pins: phosphor bronze
Plug, socket, control station shape	Angled Straight




Environment

Ambient air temperature for operation	-25...75 °C
Outlet standard	Industrial
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133 AS/NZS 3123

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.1 cm
Package 1 Width	10.1 cm
Package 1 Length	10.2 cm
Package 1 Weight	0.604 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes