

## Product data sheet

### Characteristics

# 5750WPL-GY

C-Bus Control and Management System,  
Passive Infrared Sensor, 110deg



### Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Occupancy sensor
Device application	Lighting
Sensor type	PIR
Product specific application	Staircase monitoring
Colour	Grey

### Complementary

[Ue] rated operational voltage	15...36 V DC
[In] rated current	18 mA
Communication network type	C-Bus 100
Number of channels	1
Type of setting	Light sensitivity adjustable
Light intensity adjustment	1 lux user selectable
Data backed up	Non-volatile memory
Local signalling	LED for status
Timer resolution	1 s
Warm-up time	5 s
Horizontal detection angle	0...110 °
Time delay range	0...1 s (switch-on)
Duty cycle	1090 min
Detection face	Lateral: 12 m Frontal: 18 m
C Bus termination	2 flying leads
Material	Plastic
Device mounting	Surface
Mounting support	Wall Ceiling
Mounting height	2.4 m
Fixing center	84 mm
Width	74 mm
Height	111 mm
Depth	138 mm
Colour code	GY

### Environment

IP degree of protection	IP66
Ambient air temperature for operation	0...45 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.6 cm
Package 1 Width	17.6 cm
Package 1 Length	24.8 cm
Package 1 Weight	340 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	18.2 cm
Package 2 Width	30.8 cm
Package 2 Length	45.3 cm
Package 2 Weight	3.6 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>