

Product data sheet

Characteristics

5751L-WE

C-Bus Control and Management System, Passive Infrared Occupancy Sensor



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Occupancy sensor
Device application	Lighting
Product specific application	Staircase monitoring
Sensor type	PIR
Colour	White electric

Complementary






Protection type	Creep zone protection
Type of setting	Light sensitivity adjustable
Number of channels	1
Detection face	Lateral: 6 m Frontal: 8.5 m
Movement detection area	6 m
Horizontal detection angle	0...120 °
Vertical detection angle	90 °
Time delay range	0...1 s (switch-on)
Duty cycle	1080 min
Material	Plastic
Device mounting	Surface
Mounting height	2.4 m
Colour code	WE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	12.0 cm
Package 1 Length	11.7 cm
Package 1 Weight	180.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.9 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	320
Package 3 Height	120.0 cm

Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	88.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins