

# Product data sheet

## Characteristics

# 6220-0

## FAN EXH EXPRESSAIRE 250MM



### Main

Product brand	Clipsal
---------------	---------

### Complementary

[Ue] rated operational voltage	240 V AC
Air flow	800 m3/h
Diameter	254 mm impeller:
Power consumption in W	38 W
[In] rated current	0.17 A full load

### Packing Units

Package 1 Weight	2385.000 g
Package 1 Height	150.000 mm
Package 1 width	330.000 mm
Package 1 Length	330.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.