

Product data sheet

Characteristics

624TM-WH

DIMMER 450VA TRAILNG EDGE MECHANISM

Main

Range of product	PDL 600 Designer Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate
Load type	Resistive
Colour	White

Complementary

Power consumption in VA	450 VA
[Ue] rated operational voltage	220...240 V AC
Network frequency	50 Hz
Control type	Rotary knob

Environment

Standards	AS/NZS 3100 AS/NZS 3133 CISPR 15
-----------	--

Packing Units

Package 1 Weight	0.046 kg
------------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.