

Product data sheet

Characteristics

A9C30831

impulse relay iTL - 1P - 1NO - 32A - coil 110
VDC - 230...240 VAC 50/60Hz



Main

Range of product	Acti 9
Product name	Acti 9 iTL
Product or component type	Impulse relay
Device short name	ITL
Device application	Standard
Poles	1P
Pole contact composition	1 NO
[In] rated current	32 A
Network type	AC
[Uc] control circuit voltage	230...240 V AC 50/60 Hz 110 V DC

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	250 V AC 50/60 Hz
Control type	Coil deconnection Remote and manual control
Control signal type	Impulse
Switching frequency	100 switching operations/day 5 switching operations/minute
Impulse duration	50 ms...1 s
Remote control type	Illuminated push-button
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical durability	AC-21: 50000 cycles AC-22: 20000 cycles
Connections - terminals	Control circuit: tunnel type terminals 1 cable(s) 0.5...4 mm ² rigid Control circuit: tunnel type terminals 1 cable(s) 0.5...4 mm ² rigid with cable end Control circuit: tunnel type terminals 1 cable(s) 1...4 mm ² flexible Control circuit: tunnel type terminals 1 cable(s) 1...4 mm ² flexible with ferrule Control circuit: tunnel type terminals 1 cable(s) 1.5...10 mm ² rigid Control circuit: tunnel type terminals 1 cable(s) 1.5...10 mm ² rigid with cable end Control circuit: tunnel type terminals 1 cable(s) 1.5...10 mm ² flexible Control circuit: tunnel type terminals 1 cable(s) 1.5...10 mm ² flexible with ferrule
Wire stripping length	11 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Tightening torque	1.2 N.m
Range compatibility	IATeT IATL4 IATLc IATLc+S IATLm IATLs IATLz IATLc+C IATL24 IETL iTL 32

Environment

Standards	EN 669-1 EN 669-2-2
Product certifications	GOST
Quality labels	VDE IMQ KEMA NF CEBEC
Noise level	60 dB
IP degree of protection	IP20 conforming to IEC 60529 (on opening) IP40 conforming to IEC 60529 (in enclosure)
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Package 1 Weight	0.100 kg
Package 1 Height	0.800 dm
Package 1 width	0.200 dm
Package 1 Length	0.650 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------