

Product data sheet

Characteristics

7106A

FAN EXH WALL 200MM-AUTO LOUVRE



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	600 m3/h
Diameter	188 mm impeller:
Power consumption in W	38 W
[In] rated current	0.18 A full load

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Package 1 Weight	2.860 kg
Package 1 Height	214.000 mm
Package 1 width	284.000 mm
Package 1 Length	284.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile