

Product data sheet

Characteristics

7106A

FAN EXH WALL 200MM-AUTO LOUVRE



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	600 m3/h
Diameter	188 mm impeller:
Power consumption in W	38 W
[In] rated current	0.18 A full load



Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Package 1 Weight	2.860 kg
Package 1 Height	214.000 mm
Package 1 width	284.000 mm
Package 1 Length	284.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration