

## Product data sheet

### Characteristics

# 8010LLM-WE

Modena/Strato, Single Socket 10A, 250V  
Round Earth



### Main

Range of product	Series 80
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	31 mm
Width	49.8 mm
Height	44.8 mm

### Environment

Standards	AS/NZS 3112
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	4.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	0.05 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	62 cm
Package 2 Width	86 cm
Package 2 Length	126 cm
Package 2 Weight	0.5 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	130 cm
Package 3 Width	185 cm
Package 3 Length	330 cm
Package 3 Weight	5 kg

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>