

Product data sheet

Characteristics

900/25/16EE-WE

ELBOW EXTERN TRUNKING 25X16



Main

Colour	White electric
Product brand	Clipsal
Range of product	Series 900

Complementary

Colour code	WE
Width	43 mm
Depth	29 mm
Material	PVC (polyvinyl chloride)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	13.0 g
Package 1 Height	3 cm
Package 1 width	4.3 cm
Package 1 Length	4.3 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.164 kg
Package 2 Height	7.4 cm
Package 2 width	9.8 cm
Package 2 Length	12 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	3.4 kg
Package 3 Height	25 cm
Package 3 width	21.4 cm
Package 3 Length	33.8 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile