

Product data sheet

Characteristics

9020THF-BK

Conduit, Clipsal - Cable Management, Rigid Turbo HFT H/D, 20mm 4 Meters

Main

| | |
|---------------|---------|
| Colour | Black |
| Product brand | Clipsal |

Complementary

| | |
|-------------------|--------------------|
| Colour code | BK |
| Material | PP (polypropylene) |
| Stub stiffness | Rigid |
| Diameter | Internal: 14.2 mm |
| External diameter | 20 mm |

Environment

| | |
|---------------------------------------|---|
| Environmental characteristic | Flame retardant Conforming to AS/NZS 61386 |
| Ambient air temperature for operation | -5...120 °C |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.0 cm |
| Package 1 Width | 2.0 cm |
| Package 1 Length | 400.0 cm |
| Package 1 Weight | 0.488 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.