

## Product data sheet

### Characteristics

# A9A26919

Auxiliary contact, Acti9, iSD+OF, 2 C/O, 2mA to 100mA, 24VAC to 250VAC, 24VDC to 220VDC, top and bottom connection

### Main

Range of product	Acti9
Product or component type	OC and fault contact
Device short name	iSD+OF
Signal contacts composition	2 C/O
[In] rated current	2...100 MA at 24...240 V, AC 50/60 Hz 2...100 MA at 24 V, DC 2...100 MA at 48 V, DC 2...100 MA at 60 V, DC 2...100 MA at 130 V, DC 2...100 mA at 220 V, DC
9 mm pitches	1
Standards	EN/IEC 60947-5-1 EN/IEC 60947-5-4 GB/T 14048.5 GB/T 14048.17
Product certifications	CE[RETURN]UKCA
Quality labels	EAC CCC

### Complementary

Operating mode	Daisy chain up to 100 devices
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Local signalling	Mechanical indicator
Mounting mode	Clip-on
Mounting location	Left side of circuit-breaker
Mounting support	DIN rail
Comb busbar and distribution block compatibility	NO
Height	90 mm
Width	9 mm
Depth	73 mm
Net weight	40 g
Colour	White
Connections - terminals	Screw clamp terminal (top and bottom) 1 cable(s) 1...4 mm <sup>2</sup> - rigid Screw clamp terminal (top and bottom) 1 cable(s) 0.5...2.5 mm <sup>2</sup> - flexible Screw clamp terminal (top and bottom) 2 cable(s) 2.5 mm <sup>2</sup> - rigid Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule
Wire stripping length	10 mm
Tightening torque	1 N.m top or bottom

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.100 cm
Package 1 Width	8.000 cm
Package 1 Length	9.400 cm
Package 1 Weight	49.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	663.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	7.310 kg

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1