

## Product data sheet

### Characteristics

# A9E18073

Linear switch, Acti9, 1 C/O, 20A, 250 V AC, 3 positions



### Main

Range of product	Acti9
Product name	Acti9 iSSW
Product or component type	Changeover switch
Device short name	iSSW
Device application	Electrical circuit control
Poles description	1P
Contacts type and composition	1 C/O
[Ue] rated operational voltage	250 V AC 50/60 Hz
Standards	IEC 60669-1 IEC 60947-5-1

### Complementary

[Ie] rated operational current	20 A
Control type	Toggle 3 positions
Marking	1 - 0 - 2
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	75 mm
Colour	White
Electrical durability	AC-22: 30000 cycles cos Phi = 0.8
Connections - terminals	Staggered tunnel terminal (downside) 2 cable(s) 0.5...2.5 mm <sup>2</sup> flexible Staggered tunnel terminal (downside) 2 cable(s) 0.5...2.5 mm <sup>2</sup> rigid without cable end
Wire stripping length	9 mm
Tightening torque	1 N.m

### Environment

IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Pollution degree	3
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	1.8 cm
Package 1 Length	8.2 cm

Package 1 Weight	45 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	7.8 cm
Package 2 Width	9.8 cm
Package 2 Length	23.3 cm
Package 2 Weight	592 g
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.816 kg

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------