

## Product data sheet

### Characteristics

# A9C32116

extension iETL iTL 16 - 2P - 1C/O + 1NO - 16A  
- coil 12VDC - 24VAC 50/60Hz



#### Main

Range of product	Acti 9
Product or component type	Extension for impulse relay
Device short name	IETL iTL 16
Relay application	Remote control
Poles description	2P
Pole contact composition	1 C/O + 1 NO
[In] rated current	16 A
Network type	AC

#### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
Control type	Toggle Remote control
Control signal type	Impulse
Switching frequency	5 switching operations/minute
Impulse duration	50 ms
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
[Uc] control circuit voltage	24 V AC 50/60 Hz 12 V DC
Supply inrush power	19 VA
Mounting mode	Fixed, on right side of TL
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	60 mm
Width	18 mm
Depth	84 mm
Colour	White
Electrical durability	AC-21: 200000 cycles AC-22: 100000 cycles
Connections - terminals	Tunnel type terminals - <= 6 mm <sup>2</sup>
Auxiliary connection terminal	Tunnel type terminals control circuit in 0.5...6 mm <sup>2</sup>
Range compatibility	Acti9 iTL iTL Acti9 iTL iTLi
Product compatibility	ITL 16A

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN 669-2-2 EN 669-1
Product certifications	GOST
Quality labels	CEBEC KEMA IMQ VDE NF
Noise level	60 dB
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	114.0 g
Package 1 Height	2.8 cm
Package 1 width	7.8 cm
Package 1 Length	9.4 cm
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Weight	10.014 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	1.046 kg
Package 3 Height	8.7 cm
Package 3 width	10 cm
Package 3 Length	26.7 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------