

Product data sheet

Characteristics

A9E18327

Acti9 iIL Three-phase voltage indicator light - Red - 230-400 Vac



Main

Range of product	Acti 9
Product name	Acti 9 iIL
Product or component type	Modular pilot lighth
Device short name	IIL
[Us] rated supply voltage	230...400 V AC at 50/60 Hz

Complementary

Flashing frequency	2 Hz
Indicator light	3 LEDs red, service life 100000 h of constant lighting efficiency (consumption 0.9 W)
Mounting mode	Fixed
Mounting support	Symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside: ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary connection terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm ² Tunnel type terminal 2 cable(s) rigid 2.5 mm ² Tunnel type terminal 1 cable(s) flexible 0.5 mm ² Tunnel type terminal 2 cable(s) flexible 2.5 mm ² Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm ²
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Standards	IEC 73 IEC 1000-4
IP degree of protection	IP2 IPxx B
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	49 g
Package 1 Height	1.7 cm
Package 1 width	6.8 cm
Package 1 Length	9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Weight	652 g
Package 2 Height	8 cm
Package 2 width	10 cm
Package 2 Length	23 cm
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Weight	6.355 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------