

## Product data sheet

### Characteristics

# A9F44204

Miniature circuit breaker (MCB), Acti9, iC60N  
 Disbo, 2P, 4A, C curve, 6000A (IEC/EN  
 60898-1), 25kA (IEC/EN 60947-2)



### Main

Range	Acti9
Product name	Disbo iC60
Product or component type	Miniature circuit-breaker
Device short name	IC60N
Poles description	2P
Number of protected poles	2
[In] rated current	4 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	50 KA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 KA Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 KA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 KA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 KA Icu at <= 125 V DC conforming to EN/IEC 60947-2 6000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1
Utilisation category	Category A conforming to EN/IEC 60947-2

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	440 V AC 50/60 Hz
Magnetic tripping limit	8 x In +/- 20 %
[Ics] rated service breaking capacity	50 KA 100 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 50 KA 100 % conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz 50 KA 100 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 25 KA 100 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 6000 A 100 % conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz 6 kA 100 % conforming to EN/IEC 60947-2 - 100...133 V DC
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	Rail
9 mm pitches	4
Height	85 mm
Width	36 mm

Depth	78.5 mm
Net weight	0.25 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Single terminal (top or bottom) 1...25 mm <sup>2</sup> rigid Single terminal (top or bottom) 1...16 mm <sup>2</sup> flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Separate block

## Environment

Standards	EN/IEC 60947-2 EN/IEC 60898-1
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.5 cm
Package 1 Length	9.0 cm
Package 1 Weight	221.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	66
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	15.8 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins