

## Product data sheet

### Characteristics

# A9F44263

Miniature circuit breaker (MCB), Acti9 iC60N  
Disbo, 2P, 63A, C curve, 6000A (IEC/EN  
60898-1), 10kA (IEC/EN 60947-2)



### Main

|                           |   |
|---------------------------|---|
| Range                     | Acti9   |
| Product name              | Disbo iC60  |
| Product or component type | Miniature circuit-breaker   |
| Device short name         | IC60N   |
| Poles description         | 2P  |
| Number of protected poles | 2   |
| [In] rated current        | 63 A  |
| Network type              | AC/DC   |
| Trip unit technology      | Thermal-magnetic  |
| Curve code                | C   |
| Breaking capacity         | 10 KA Icu at <= 125 V DC conforming to EN/IEC 60947-2<br>6000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1<br>36 KA Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>20 KA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>10 KA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>6 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 |
| Utilisation category      | Category A conforming to EN/IEC 60947-2   |

### Complementary

|  |  |
|--|--|
| Network frequency                      | 50/60 Hz   |
| [Ue] rated operational voltage         | 440 V AC 50/60 Hz  |
| Magnetic tripping limit                | 8 x In +/- 20 %  |
| [Ics] rated service breaking capacity  | 27 KA 75 % conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz<br>15 KA 75 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz<br>7.5 KA 75 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz<br>4.5 KA 75 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz<br>6000 A 100 % conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz<br>6 kA 100 % conforming to EN/IEC 60947-2 - 100...133 V DC |
| Limitation class                       | 3 conforming to EN/IEC 60947-2   |
| [Ui] rated insulation voltage          | 500 V AC 50/60 Hz  |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN/IEC 60947-2  |
| Contact position indicator             | Yes  |
| Control type                           | Toggle   |
| Local signalling                       | Trip indicator   |
| Mounting mode                          | Clip-on  |
| Mounting support                       | Rail   |
| 9 mm pitches                           | 4  |
| Height                                 | 85 mm  |
| Width                                  | 36 mm  |
| Depth                                  | 78.5 mm  |

|                          |   |
|--------------------------|---|
| Net weight               | 0.25 kg   |
| Colour                   | White   |
| Mechanical durability    | 20000 cycles  |
| Electrical durability    | 10000 cycles  |
| Provision for padlocking | Padlockable   |
| Connections - terminals  | Single terminal (top or bottom) 1...35 mm <sup>2</sup> rigid<br>Single terminal (top or bottom) 1...25 mm <sup>2</sup> flexible |
| Wire stripping length    | 14 mm for top or bottom connection  |
| Tightening torque        | 3.5 N.m top or bottom   |
| Earth-leakage protection | Separate block  |






## Environment

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Standards                             | EN/IEC 60947-2<br>EN/IEC 60898-1 |
| IP degree of protection               | IP20 conforming to IEC 60529     |
| Pollution degree                      | 3 conforming to EN/IEC 60947-2   |
| Tropicalisation                       | 2 conforming to IEC 60068-1      |
| Relative humidity                     | 95 % at 55 °C                    |
| Ambient air temperature for operation | -35...70 °C                      |
| Ambient air temperature for storage   | -40...85 °C                      |

## Packing Units

|                              |                  |
|------------------------------|------------------|
| Unit Type of Package 1       | Db               |
| Number of Units in Package 1 | 1                |
| Package 1 Height             | 3.600 cm         |
| Package 1 Width              | 7.500 cm         |
| Package 1 Length             | 8.900 cm         |
| Package 1 Weight             | 258.000 g        |
| Unit Type of Package 2       | Gyári csomagolás |
| Number of Units in Package 2 | 6                |
| Package 2 Height             | 8.000 cm         |
| Package 2 Width              | 9.500 cm         |
| Package 2 Length             | 22.000 cm        |
| Package 2 Weight             | 1.605 kg         |
| Unit Type of Package 3       | Doboz            |
| Number of Units in Package 3 | 66               |
| Package 3 Height             | 30.000 cm        |
| Package 3 Width              | 30.000 cm        |
| Package 3 Length             | 40.000 cm        |
| Package 3 Weight             | 17.850 kg        |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  Yes   |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins       |