

Product data sheet

Characteristics

A9E18034

Acti9 iPB 1NO-1NC double push button green/red



Main

Range of product	Acti 9
Product name	Acti 9 iPB
Product or component type	Push-button
Device short name	IPB
Standards	IEC 60947-5-1 IEC 60669-1

Complementary

Contacts type and composition	1 NC 1 NO
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	2 push-button green/red
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside: Clario Upside: Librio Upside: ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - terminals	Staggered tunnel terminal1 cable(s) 0.5 mm ² rigid Staggered tunnel terminal1 cable(s) 0.5 mm ² flexible Staggered tunnel terminal1 cable(s) 0.5 mm ² flexible with ferrule Staggered tunnel terminal2 cable(s) 2.5 mm ² rigid Staggered tunnel terminal2 cable(s) 2.5 mm ² flexible Staggered tunnel terminal2 cable(s) 2.5 mm ² flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------