

# Product data sheet

## Characteristics

# A9E18034

Double push button, Acti9, 1NO-1NC green/red



### Main

Range of product	Acti9
Product name	Acti9 iPB
Product or component type	Push-button
Device short name	iPB
Standards	IEC 60947-5-1 IEC 60669-1

### Complementary

Contacts type and composition	1 NC 1 NO
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	2 push-button green/red
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside: Clario Upside: Librio Upside: ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - terminals	Staggered tunnel terminal1 cable(s) 0.5 mm <sup>2</sup> rigid Staggered tunnel terminal1 cable(s) 0.5 mm <sup>2</sup> flexible Staggered tunnel terminal1 cable(s) 0.5 mm <sup>2</sup> flexible with ferrule Staggered tunnel terminal2 cable(s) 2.5 mm <sup>2</sup> rigid Staggered tunnel terminal2 cable(s) 2.5 mm <sup>2</sup> flexible Staggered tunnel terminal2 cable(s) 2.5 mm <sup>2</sup> flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

### Environment

Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	2.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	46.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.200 cm
Package 2 Width	10.000 cm
Package 2 Length	23.500 cm
Package 2 Weight	612.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.987 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------