

## Product data sheet

### Characteristics

# A9E18326

Acti9, iLL Blinker indicator light - Red - 110-230 Vac



### Main

Range of product	Acti9
Product name	Acti9 iLL
Product or component type	Modular pilot lighth
Device short name	iLL
[Us] rated supply voltage	110...230 V AC at 50/60 Hz

### Complementary

Flashing frequency	2 Hz
Indicator light	1 blinker red, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Mounting mode	Fixed
Mounting support	Symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside: ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary connection terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) rigid 2.5 mm <sup>2</sup> Tunnel type terminal 1 cable(s) flexible 0.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) flexible 2.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm <sup>2</sup>
Wire stripping length	9 mm
Tightening torque	1 N.m





### Environment

Standards	IEC 60947-5-1
IP degree of protection	IP2 IPxx B
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.800 cm
Package 1 Width	1.700 cm
Package 1 Length	9.000 cm
Package 1 Weight	44.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	9.800 cm
Package 2 Width	8.000 cm
Package 2 Length	23.200 cm
Package 2 Weight	566.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.811 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts & cables product

## Contractual warranty

Warranty	18 months
----------	-----------