

## Product data sheet

### Characteristics

# A9E18334

Acti9 iIL single indicator light - Yellow - 12-48  
Vac/dc



### Main

Range of product	Acti 9
Product name	Acti 9 iIL
Product or component type	Modular pilot light
Device short name	IIL
[Us] rated supply voltage	12...48 V AC at 50/60 Hz 12...48 V DC

### Complementary

Flashing frequency	2 Hz
Indicator light	1 LED yellow, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Mounting mode	Fixed
Mounting support	Symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside: ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary connection terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) rigid 2.5 mm <sup>2</sup> Tunnel type terminal 1 cable(s) flexible 0.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) flexible 2.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm <sup>2</sup>
Wire stripping length	9 mm
Tightening torque	1 N.m

### Environment

Standards	IEC 60947-5-1
IP degree of protection	IP2 IPxx B
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------